

Part No: 3777-906

Fabricated DWV

Combo Wye & 1/8 Bend

Desc: 24X6 PVC RED COMB WYE&1/8 BEND SOC SCH40

MSRP: 3277.71

Part Code: 390

Weight(lbs): 131.814

Weight(kg): 59.79

Weight(gm): 59790


Size: 24 X 6

Color: WHITE

Material: PVC

Schedule SCH 40 DWV- Reducing

Connection Socket x Socket x Socket



L = 45-1/2

M = 25-3/8

M1 = 7-1/4

G1 = 3-3/4

G2 = 17-3/4

G3 = 21

H = 24

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

