

Part No: 3777-908

Fabricated DWV

Combo Wye & 1/8 Bend

Desc: 24X8 PVC RED COMB WYE&1/8 BEND SOC SCH40

MSRP: 3656.36

Part Code: 390

Weight(lbs): 144.491

Weight(kg): 65.54

Weight(gm): 65540


Size: 24 X 8

Color: WHITE

Material: PVC

Schedule SCH 40 DWV- Reducing

Connection Socket x Socket x Socket



G1 = 2-13/16

G2 = 21-11/16

G3 = 23-7/16

H = 27-1/2

L = 48-1/2

M = 25-3/8

M1 = 9-3/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

