

Part No: 3790-910

Fabricated DWV

Sanitary Tee

Desc: 24X10 PVC RED SAN TEE SOC SCH40 N.P.R.

MSRP: 3884.86

Part Code: 390

Weight(lbs): 161.041


Weight(kg): 73.047

Weight(gm): 73047

Size: 24"X24"X10"

Color: WHITE

Material: PVC



Type Sch 40 DWV- Reducer
Connection Socket X Socket X Socket

G1 = 7

G2 = 19-3/4

G3 = 25-7/16

H = 30-11/16

L = 50-3/4

M = 25-3/8

M1 = 11-1/2

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

