

Part No: 3792-664

Fabricated DWV

Double Wye

Desc: 12X4 PVC RED DBL CMB Y&1/8 BND SOC SCH40

MSRP: 763.54

Part Code: 390

Weight(lbs): 27.542


Weight(kg): 12.493

Weight(gm): 12493

Size: 12"X12"X4"X4"

Color: WHITE

Material: PVC



Schedule SCH 40 DWV

Type Reducing Double Combo Wye
With 1/8 Bend

Connection Socket x Socket x Socket x Socket

G1 = 1-1/16

G2 = 12-7/16

G3 = 14-1/4

M1 = 5-1/16

H1 = 16

L = 26

M = 13-9/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

