

**Part No:** 3901-696C

**Fabricated CPVC Schedule 80 Tees  
DWV**

**Desc:** 14X6 CPVC RED TEE SOC SCH80

**MSRP:** 4939.91

**Part Code:** 099

**Weight(lbs):** 64.353

**Weight(kg):** 29.19

**Weight(gm):** 29190


**Size:** 14 X 6

**Color:** GRAY

**Material:** CPVC

**Type** Reduction

**Connection** Socket x Socket x Socket



**G** = 8-1/4

**G1** = 10-1/2

**H** = 15-1/4

**H1** = 13-3/4

**L** = 30-1/2

**M** = 15-1/2

**M1** = 7-1/2

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

