

Part No: 3901-912

Fabricated DWV

Tees

Desc: 24X12 PVC RED TEE SOC SCH80

MSRP: 4448.49

Part Code: 400

Weight(lbs): 269.969


Weight(kg): 122.456

Weight(gm): 122456

Size: 24 X 12

Color: GRAY

Material: PVC



Type Reducing Vent Tee
Schedule SCH 80 DWV
Connection Socket x Socket x Socket

L = 48-1/2

M = 26-7/16

M1 = 14-1/8

G = 12-1/4

G1 = 15-15/16

H = 24-1/4

H1 = 22-3/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.


L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006