Spears® Technical Information

10-Sep-21 11:11:14 PM

Part No: 3920-240 **Fabricated DWV** **Crosses**

Desc: 24 PVC CROSS SOC SCH80

MSRP: 11520.49 **Part Code:** 400

Weight(lbs): 553.715 **Weight(kg):** 251.161 **Weight(gm):** 251161

Size: 24 **Color:** GRAY **Material:** PVC



Type Standard

Schedule SCH 80 DWV

Connection Soc x Soc x Soc x Soc

H1 = 32-1/4 **H** = 32-1/4 **G1** = 20-1/4 **G** = 20-1/4 **L** = 64-1/2

L1 = 64-1/2 **M** = 26-7/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References









The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained thereform. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006