

Part No: 3929-532

Fabricated DWV

Couplings

Desc: 6X4 PVC RED COUPLING SOC SCH80

MSRP: 142.57

Part Code: 400

Weight(lbs): 2.69

Weight(kg): 1.22

Weight(gm): 1220

Size: 6 X 4

Color: GRAY

Material: PVC

Schedule SCH 80 DWV - Reducing

Connection Socket x Socket



L = 8-7/8

M = 7-5/16

M1 = 5-3/16

N = 3-3/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

