

Part No: 3929-788

Fabricated DWV

Couplings

Desc: 18X8 PVC RED COUPLING SOC SCH80

MSRP: 2457.01

Part Code: 400

Weight(lbs): 89.682

Weight(kg): 40.679

Weight(gm): 40679

Size: 18 X 8

Color: GRAY

Material: PVC

Schedule SCH 80 DWV - Reducing

Connection Socket x Socket



L = 39-1/2

M = 19-11/16

M1 = 9-5/8

N = 26-1/4

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

