

Part No: 3965-700

Fabricated DWV

Glue-on Saddles

Desc: 14X10 PVC STUB SADDLE SOC SCH80 N.P.R.

MSRP: 445.68

Part Code: 400

Weight(lbs): 20.144

Weight(kg): 9.137

Weight(gm): 9137

Size: 14 X 10

Color: GRAY

Material: PVC

Schedule SCH 80 DWV Stub Saddle

Connection Socket



H = 17-3/8

L = 19-1/2

M = 11-15/16

N = 5-1/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.
- L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; ± 1/4 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.
- W** = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

