

Part No: 3975-788

Fabricated DWV

Wyes

Desc: 18X8 PVC RED WYE SOC N.P.R. SCH80

MSRP: 2689.47

Part Code: 400

Weight(lbs): 127.169

Weight(kg): 57.683

Weight(gm): 57683

Size: 18 X 8


Color: GRAY

Material: PVC

Schedule SCH 80 DWV

Connection Socket X Socket X Socket

Type Reducing Wye



M1 = 9-5/8

H1 = 12

H2 = 30

G1 = 3

G2 = 21

G3 = 21-7/8

H3 = 26-1/8

L = 42

M = 19-7/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

