

Part No: 3975-906C

**Fabricated CPVC Schedule 80 Wyes
DWV**

Desc: 24X6 CPVC RED WYE SOC SCH80 N.P.R.

MSRP: 19183.77

Part Code: 099

Weight(lbs): 277.324

Weight(kg): 125.792

Weight(gm): 125792


Size: 24 X 6

Color: GRAY

Material: CPVC

Type Reducing

Connection Socket x Socket x Socket



H3 = 27-1/16

L = 46-1/4

M = 26-7/16

M1 = 7-1/2

H1 = 11-1/8

H2 = 35-1/8

G1 = 7/8

G2 = 23-1/8

G3 = 23-13/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.


L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006