

Part No: 3975-916

Fabricated DWV

Wyes

Desc: 24X16 PVC RED WYE SOC SCH80 N.P.R.

MSRP: 6970.76

Part Code: 400

Weight(lbs): 375.743

Weight(kg): 170.434

Weight(gm): 170434

Size: 24 X 16


Color: GRAY

Material: PVC

Schedule SCH 80 DWV

Connection Socket X Socket X Socket

Type Reducing Wye



G1 = 7-3/4

G2 = 31-3/4

G3 = 31-1/4

H3 = 39-1/4

L = 63-1/2

M = 26-7/16

M1 = 17-11/16

H1 = 19-3/4

H2 = 43-3/4

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

