

Part No: 3977-664

Fabricated DWV

Combo Wye & 1/8 Bend

Desc: 12X4 PVC RED COMB WYE&1/8 BEND SOC SCH80

MSRP: 1110.73

Part Code: 400

Weight(lbs): 45.195

Weight(kg): 20.5

Weight(gm): 20500


Size: 12 X 4

Color: GRAY

Material: PVC

Schedule SCH 80 DWV-Reducing

Connection Socket x Socket x Socket



G3 = 13-1/8

H = 15-7/16

L = 26-1/2

M = 14-1/8

M1 = 5-1/4

G1 = 1-1/4

G2 = 12-3/4

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

