

Part No: 401-790F

Fabricated Fittings

Tees

Desc: 18X10 PVC RED TEE SOC SCH40

MSRP: 2954.66

Part Code: 047

Weight(lbs): 107.588

Weight(kg): 48.801

Weight(gm): 48801

Size: 18"X18"X10"


Color: WHITE

Material: PVC

Schedule Schedule 40

Connection Socket X Socket X Socket

Type Reduction



G = 10- 3/4

G1 = 12-13/16

G2 = 10- 3/4

H = 19- 3/4

H1 = 18- 1/16

H2 = 19- 3/4

L = 39- 1/2

M = 19- 1/8

M1 = 11- 1/2

M2 = 19- 1/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

