

Part No: 405-007

Schedule 40 White

Tee

Desc: 3/4 PVC TEE FPT SCH40

MSRP: 7.74

Part Code: 040

Weight(lbs): 0.101

Weight(kg): 0.046

Weight(gm): 46


Size: 3/4"

Color: WHITE

Material: PVC

Connection Fipt x Fipt x Fipt

Type Standard



G = 9/16

H = 1-3/8

L = 2-3/4

M = 1-9/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

