

Part No: 411-120F

Fabricated Fittings

Elbow

Desc: 12 PVC 11-1/4 ELL SOC SCH40 FAB

MSRP: 447.79

Part Code: 047

Weight(lbs): 14.103


Weight(kg): 6.397

Weight(gm): 6397

Size: 12"

Color: WHITE

Material: PVC



H = 7-13/16

J = 1-9/16

M = 13-9/16

Schedule SCH 40

Angle 11-1/4 Degree

Connection Socket X Socket

Type Standard

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

