

Part No: 412-007UV

Schedule 40 UVR

Elbow

Desc: 3/4 PVC UVR 90 ST ELL MPTXFPT SCH40

MSRP: 8.87

Part Code: 042

Weight(lbs): 0.068

Weight(kg): 0.031

Weight(gm): 31


Size: 3/4"

Color: BEIGE

Material: PVC UVR

Connection Mipt x Fipt

Type 90° Street Elbow



G = 13/16

G1 = 7/16

H = 1-17/32

H1 = 1-3/16

M1 = 1-11/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

