

**Part No:** 41203A123-120

**All**

**AV-1**

**Desc:** 12 POLYPRO STANDARD BUTTERFLY VALVE EPDM, 316SS STEM W/ 115VAC REVERSIBLE ELECTRIC ACTUATOR, NEMA 4 ENCLOSURE, 100% DUTY CYCLE, DECLUTCHABLE MANUAL OVERRIDE W/ POSITION INDICATOR

**MSRP:** 9064.4

**Part Code:** 514

**Weight(lbs):** 68.423

**Weight(kg):** 31.036

**Weight(gm):** 31036

**Size:**

**Color:**

**Material:**

**Connection** EPDM

# Under

# Development

=

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

