

Part No: 41302A123-120

All

AV-1

Desc: 12 CPVC STANDARD BUTTERFLY VALVE VITON, 316SS STEM W/ 115VAC REVERSIBLE ELECTRIC ACTUATOR, NEMA 4 ENCLOSURE, 100% DUTY CYCLE, DECLUTCHABLE MANUAL OVERRIDE W/ POSITION INDICATOR

MSRP: 14795.58

Part Code: 512

Weight(lbs): 79.929

Weight(kg): 36.255

Weight(gm): 36255

Size:

Color:

Material:

Connection FKM

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

