

Part No: 41312A123-120

All

AV-1

Desc: 12 CPVC ZINC/LUG STD BUTTERFLY VALVE FKM O-RING,115VAC REVERSIBLE
ELECTRIC ACTUATOR NEMA 4 ENCLSURE 100% DUTY CYCLE FRICTION
BRAKE,DECLUTCHABLE MANUAL OVERRIDE AND POSITION INDICATOR

MSRP: 15883.64

Part Code: 512

Weight(lbs): 85.237

Weight(kg): 38.663

Weight(gm): 38663

Size:

Color:

Material:

Connection FKM with Zinc Lug Inserts

Under

Development

=

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

