

Part No: 420-626F

Fabricated Fittings

Cross

Desc: 10X6 PVC RED CROSS SOC SCH40 FAB

MSRP: 1340.77

Part Code: 047

Weight(lbs): 26.5


Weight(kg): 12.02

Weight(gm): 12020

Size: 10"X10"X6"X6"

Color: WHITE

Material: PVC



Schedule SCH 40
Connection Socket X Socket
Type Reduction

G = 6- 7/8 **G1** = 8- 3/8 **H** = 12- 1/8 **M1** = 7- 3/16 **H1** = 11- 5/8
L = 24- 1/4 **L1** = 23- 1/4 **M** = 11- 1/2

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.
- L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; ± 1/4 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.
- W** = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

