

Part No: 420-901F

Fabricated Fittings

Cross

Desc: 24X2 PVC RED CROSS SOC SCH40 FAB

MSRP: 4213.81

Part Code: 047

Weight(lbs): 96.031


Weight(kg): 43.559

Weight(gm): 43559

Size: 24"X24"X2"X2"

Color: WHITE

Material: PVC



Schedule SCH 40
Connection Socket X Socket
Type Reduction

G = 8- 1/8 **G1** = 14- 5/16 **H** = 20- 1/8 **H1** = 16- 1/16 **L** = 40- 1/4
L1 = 32- 1/8 **M** = 25- 3/8 **M1** = 2-11/16

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.
- L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; ± 1/4 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.
- W** = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

