

Part No: 429-010N

Schedule 40 White

Coupling

Desc: 1 PVC COUPLING SOC NESTING SCH40

MSRP: 1.71

Part Code: 040

Weight(lbs): 0.097


Weight(kg): 0.044

Weight(gm): 44

Size: 1"

Color: WHITE

Material: PVC



Connection Socket x Socket

Type Standard

L = 2-3/8

N = 3/32

M = 1-21/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

