

Part No: 429-422F

Fabricated Fittings

Coupling

Desc: 4X3 PVC RED COUPLING SOC SCH40

MSRP: 63.1

Part Code: 047

Weight(lbs): 1.076

Weight(kg): 0.488

Weight(gm): 488

Size: 4 X 3


Color: WHITE

Material: PVC

Schedule SCH 40

Connection Socket X Socket

Type Reduction



L = 6-1/2

M = 4-15/16

M1 = 3-15/16

N = 2

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

