

Part No: 429-534F

Fabricated Fittings

Coupling

Desc: 6X4-1/2 PVC RED COUPLING SOC SCH40

MSRP: 140.98

Part Code: 047

Weight(lbs): 2.041

Weight(kg): 0.926

Weight(gm): 926

Size: 6"X4-1/2"


Color: WHITE

Material: PVC

Schedule SCH 40

Connection Socket X Socket

Type Reduction



L = 8-11/16

M = 7-1/8

M1 = 5-7/16

N = 2-15/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

