

Part No: 429-786F

Fabricated Fittings

Coupling

Desc: 18X6 PVC RED COUPLING SOC SCH40

MSRP: 1792.63

Part Code: 047

Weight(lbs): 50.336

Weight(kg): 22.832

Weight(gm): 22832

Size: 18"X6"


Color: WHITE

Material: PVC

Schedule SCH 40

Connection Socket X Socket

Type Reduction



L = 38

M = 19

M1 = 7- 3/16

N = 25- 3/4

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

