

Part No: 4301-820C

Fume & Air Duct

Tee

Desc: 20X10 CPVC RED TEE SOC DUCT

MSRP: 2230.91

Part Code: 432

Weight(lbs): 20.988

Weight(kg): 9.52

Weight(gm): 9520


Size: 20X10

Color: GRAY

Material: CPVC

Type Reducing Tee

Connection Belled Socket



G = 9-3/4

G1 = 13-3/4

H = 12-1/4

H1 = 16-1/4

L = 24-1/2

M = 20-7/16

M1 = 11-1/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

