

Part No: 4306-160C

Fume & Air Duct

Elbow

Desc: 16 CPVC 90 ELL SOC DUCT

MSRP: 1435.58

Part Code: 432

Weight(lbs): 17.747

Weight(kg): 8.05

Weight(gm): 8050


Size: 16

Color: GRAY

Material: CPVC

Type 90° Elbow 2-Piece

Connection Belled Socket



G = 13-11/16

H = 16-3/16

M = 16-3/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

