

Part No: 4329C-912C

Fume & Air Duct

Coupling

Desc: 24X12 CPVC CONICAL REDUCER SOC DUCT

MSRP: 2004.34

Part Code: 433

Weight(lbs): 8.79

Weight(kg): 3.987

Weight(gm): 3987


Size: 24X12

Color: GRAY

Material: CPVC

Type Conical Reducer Coupling

Connection Belled Socket



L = 20-1/2

M = 24-1/2

M1 = 13-1/8

N = 15-1/2

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

