

Part No: 435-060G

Schedule 40 Gray

Adapter

Desc: 6 PVC FEMALE ADAPTER SOCXFPT SCH40

MSRP: 97.87

Part Code: 043

Weight(lbs): 2.121

Weight(kg): 0.962

Weight(gm): 962


Size: 6"

Color: GRAY

Material: PVC

Connection Socket x Fipt

Type Standard



L = 5-3/4

M = 7-3/16

N = 5/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

