

Part No: 435-532

All

40-1

Desc: 6X4 PVC RED FEM ADAPTER SOCXFIP T SCH40

MSRP: 128.3

Part Code: 040

Weight(lbs): 4.691

Weight(kg): 2.128

Weight(gm): 2128

Size: 6 X 4

Color:

Material:

Connection Soc x Fipt

Under

Development

L = 6-13/16

M = 7-1/4

M1 = 7-9/32

N = 2-9/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

