

Part No: 436-120F

Fabricated Fittings

Adapter

Desc: 12 PVC MALE ADAPTER MPTXSOC SCH40

MSRP: 520.53

Part Code: 047

Weight(lbs): 16.455


Weight(kg): 7.464

Weight(gm): 7464

Size: 12"

Color: WHITE

Material: PVC



L = 11- 1/8

M1 = 14- 1/8

N = 2- 3/4

Schedule SCH 40

Connection Mipt X Socket

Type Standard

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

