

Part No: 442-040

Schedule 40 White

Elbow

Desc: 4 PVC 22-1/2 ST ELL SPIGOTXSOC SCH40

MSRP: 97.67

Part Code: 040

Weight(lbs): 1.642

Weight(kg): 0.745

Weight(gm): 745

Size: 4"


Color: WHITE

Material: PVC

Connection Spigot x Socket

Angle 22-1/2°

Type Standard



H = 3

H1 = 2- 7/8

J = 1- 7/8

J1 = 5/8

M1 = 5- 1/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

