

Part No: 4423I-010P

Valves

Industrial Swing Check Valve

Desc: 1 PP SWING CHECK VALVE FLNGED EPDM W/IND

MSRP: 1150.68

Part Code: 113

Weight(lbs): 2.011

Weight(kg): 0.912

Weight(gm): 912

Size: 1"


Color: BEIGE

Material: Polypropylene

Type W/Indicator

O-Ring EPDM

Pressure Rating 150 PSI @ 73° F



A = 6- 5/8

B = 6- 5/16

C = 4- 1/4

D = 31/32

E = 4- 1/2

F = 4- 1/2

Bolt Size = 5/8

G = 3- 7/32

H = 1-21/32

I = 5/8

Cv = 24
Values

No of
Bolts = 4

Bolt = 3- 1/8
Circle
Dia.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006