

Part No: 457-005G

Schedule 40 Gray

Union

Desc: 1/2 PVC UNION SOCXSOC BUNA SCH40 GRAY

MSRP: 11.76

Part Code: 043

Weight(lbs): 0.082

Weight(kg): 0.037

Weight(gm): 37


Size: 1/2"

Color: GRAY

Material: PVC

Connection Socket x Socket

O-Ring Buna - N



L = 1-27/32

M = 1-3/32

N = 11/32

NUT = 1-23/32
O.D.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

