

**Part No:** 4721L3-005SR

**Valves**

**3-Way Ball Valve**

**Desc:** 1/2 PVC T/U IND 3WAY VERT L/3 SRTHD EPDM

**MSRP:** 344.01

**Part Code:** 615

**Weight(lbs):** 0.54

**Weight(kg):** 0.245

**Weight(gm):** 245

**Size:** 1/2"

**Color:** GRAY

**Material:** PVC



**A** = 1- 7/8

**B** = 2- 7/16

**C** = 3-13/16

**D** = 2- 9/16

**E** = 2-13/16

**F** = 2- 3/8

**G** = 1-11/16

**Type** Triple L - Port (Vertical)

**Connection** SR Fipt

**O-Ring** EPDM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

