

Part No: 4722L1-010C

Valves

3-Way Ball Valve

Desc: 1 CPVC T/U IND 3WAY VERT L/I SOC EPDM

MSRP: 375.88

Part Code: 617

Weight(lbs): 1.129


Weight(kg): 0.512

Weight(gm): 512

Size: 1"

Color: GRAY

Material: CPVC



A = 2-11/16

B = 2-15/16

C = 5-3/16

D = 3-1/16

E = 3-1/2

F = 3-5/16

G = 2-3/16

Type Single L - Port (Vertical)
Connection Socket
O-Ring EPDM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

