

**Part No:** 4722L1-040

**Valves**

**3-Way Ball Valve**

**Desc:** 4 PVC T/U IND 3WAY VERT L/1 SOC EPDM

**MSRP:** 2600.86

**Part Code:** 615

**Weight(lbs):** 21.043

**Weight(kg):** 9.545

**Weight(gm):** 9545

**Size:** 4"

**Color:** GRAY

**Material:** PVC



**F** = 8-3/16

**G** = 5-15/16

**A** = 7-3/4

**B** = 7-7/16

**C** = 11-15/16

**D** = 6-11/16

**E** = 9

**Type** Single L - Port (Vertical)  
**Connection** Socket  
**O-Ring** EPDM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

