

Part No: 4722L2-005C

Valves

3-Way Ball Valve

Desc: 1/2 CPVC T/U IND 3WAY VERT L/2 SOC EPDM

MSRP: 525.11

Part Code: 617

Weight(lbs): 0.54


Weight(kg): 0.245

Weight(gm): 245

Size: 1/2"

Color: GRAY

Material: CPVC



A = 1-15/16

B = 2-1/2

C = 4-1/4

D = 2-17/32

E = 2-7/8

F = 2-11/16

G = 1-13/16

Type Double L - Port (Vertical)
Connection Socket
O-Ring EPDM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

