

**Part No:** 4722L3-005C

**Valves**

**3-Way Ball Valve**

**Desc:** 1/2 CPVC T/U IND 3WAY VERT L/3 SOC EPDM

**MSRP:** 525.11

**Part Code:** 617

**Weight(lbs):** 0.542

**Weight(kg):** 0.246

**Weight(gm):** 246

**Size:** 1/2"

**Color:** GRAY

**Material:** CPVC



A = 1-15/16

B = 2-1/2

C = 4-1/4

D = 2-17/32

E = 2-7/8

F = 2-11/16

G = 1-13/16

**Type** Triple L - Port (Vertical)  
**Connection** Socket  
**O-Ring** EPDM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

