

Part No: 4722L3-030

Valves

3-Way Ball Valve

Desc: 3 PVC T/U IND 3WAY VERT L/3 SOC EPDM

MSRP: 1674.57

Part Code: 615

Weight(lbs): 9.584


Weight(kg): 4.347

Weight(gm): 4347

Size: 3"

Color: GRAY

Material: PVC



Type Triple L - Port (Vertical)
Connection Socket
O-Ring EPDM

A = 6-3/16

B = 7

C = 10-3/4

D = 5-7/8

E = 7-5/8

F = 6-3/4

G = 4-7/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

