

**Part No:** 4722T1-025

**Valves**

**3-Way Ball Valve**

**Desc:** 2-1/2 PVC T/U IND 3WY VERT T/PT SOC EPDM

**MSRP:** 1474.43

**Part Code:** 615

**Weight(lbs):** 9.383

**Weight(kg):** 4.256

**Weight(gm):** 4256

**Size:** 2-1/2"

**Color:** GRAY

**Material:** PVC



**A** = 5- 3/8

**B** = 5- 7/8

**C** = 9- 5/16

**D** = 5- 1/8

**E** = 6- 1/4

**F** = 5- 7/8

**G** = 4- 3/8

**S** = 13/32

**Type** T - Port (Vertical)

**Connection** Socket

**O-Ring** EPDM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

