

Part No: 4723T1-020

Valves

3-Way Ball Valve

Desc: 2 PVC T/U IND 3WAY VERT T/PT FLG EPDM

MSRP: 1336.2

Part Code: 615

Weight(lbs): 6.72


Weight(kg): 3.048

Weight(gm): 3048

Size: 2

Color: GRAY

Material: PVC



B = 4- 3/4

C = 7- 3/4

D = 4- 1/2

E = 5- 1/8

F = 6-3/8

H = 6

Type T - Port (Vertical)
Connection Flanged
O-Ring EPDM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

