

**Part No:** 4724L1-020

**All**

**INTL-1**

**Desc:** 63MM PVC TUK2 VRT 3WY BV L1/PT EPDM DIN

**MSRP:** 419.22

**Part Code:** 238

**Weight(lbs):** 3.816

**Weight(kg):** 1.731

**Weight(gm):** 1731

**Size:** 63MM

**Color:**

**Material:**

**Connection** DIN SOC with L1 Port

# Under

# Development

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

