

Part No: 4728T1-012C

All

INTL-1

Desc: 30MM JIS CPVC TUK2 VRT 3WY BV T1/PT EPDM

MSRP: 454.73

Part Code: 239

Weight(lbs): 1.821

Weight(kg): 0.826

Weight(gm): 826

Size: 30MM

Color:

Material:

Connection JIS SOC with T1 Port

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

