

**Part No:** 4731L1-010SR

**Valves**

**3-Way Ball Valve**

**Desc:** 1 PVC T/U IND 3WAY VERT L/1 SR/THD FKM

**MSRP:** 278.84

**Part Code:** 615

**Weight(lbs):** 1.113

**Weight(kg):** 0.505

**Weight(gm):** 505

**Size:** 1"

**Color:** GRAY

**Material:** PVC



**A** = 2- 9/16

**B** = 2- 7/8

**C** = 4-11/16

**D** = 3- 1/8

**E** = 3- 7/16

**F** = 3

**G** = 2- 1/8

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

