

Part No: 4731L1-040CSR

Valves

3-Way Ball Valve

Desc: 4 CPVC T/U IND 3WAY VERT L/1 SR/THD FKM

MSRP: 4147.68

Part Code: 617

Weight(lbs): 21.61


Weight(kg): 9.802

Weight(gm): 9802

Size: 4"

Color: GRAY

Material: CPVC



A = 7- 1/2

B = 7- 1/4

C = 10- 1/4

D = 6- 3/4

E = 9- 3/16

F = 6- 3/4

G = 5- 7/8

Type Single L - Port (Vertical)

Connection SR Fipt

O-Ring FKM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

