

**Part No:** 4731L1-040SR

**Valves**

**3-Way Ball Valve**

**Desc:** 4 PVC T/U IND 3WAY VERT L/1 SR/THD FKM

**MSRP:** 2695.98

**Part Code:** 615

**Weight(lbs):** 20.915

**Weight(kg):** 9.487

**Weight(gm):** 9487

**Size:** 4"

**Color:** GRAY

**Material:** PVC



A = 7- 1/2

B = 7- 1/4

C = 10- 1/4

D = 6- 3/4

E = 9- 3/16

F = 6- 3/4

G = 5- 7/8

**Type** Single L - Port (Vertical)  
**Connection** SR Fipt  
**O-Ring** FKM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

