

Part No: 4731L2-030CSR

Valves

3-Way Ball Valve

Desc: 3 CPVC T/U IND 3WAY VERT L/2 SR/THD FKM

MSRP: 2690.77

Part Code: 617

Weight(lbs): 10.337


Weight(kg): 4.689

Weight(gm): 4689

Size: 3"

Color: GRAY

Material: CPVC



A = 6- 3/16

B = 6- 7/8

C = 9- 3/4

D = 5- 7/8

E = 7- 5/8

F = 6- 3/16

G = 4- 7/8

Type Double L - Port (Vertical)
Connection SR Fipt
O-Ring FKM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

